

Arm and Femur Load Cell

Type M56516A...

Six-axial

Type M56516A... is designed to measure forces and moments in the arm of the dummy WorldSID-50 % (WS) and in the femur of the WorldSID-5 % (W5) dummy.

- Six-axial (F_x, F_y, F_z, M_x, M_y, M_z)
- UPS module available
- · Low linearity errors and hysteresis errors
- Kistler system cabling
- Polarities according to SAE J211/1



The load cells is made of a deformation body that is affected by forces and moments. Those mechanical forces and moments create streches and bucklings that cause a resistance change on the applied gaging members. This resistance change is measured as electrical signal in a bridge circuit. In order to avoid linearity errors, the deformation paths are constructively held small (high rigidity). Thus a proportional behavior is realized. The load cell is available with UPS module which is integrated in an external housing in the wiring or in the connector. Customized cable lengths and connectors with specific pin assignments are optionally available.



Application

The load cell is directly assembled at the designated location in the dummy and provides important information about the loads on the human body occurring during a crash test.

Technical Data

Axial Data		F _x	Fy	Fz	M _x	My	Mz
Measuring range	kN	9,0	9,0	13,5			
	N⋅m				225	225	170
Bridge output voltage (typ.)	mV/V	2,1	2,1	1,35	2,1	2,1	3,1
Sensitivity (typ.)	μV/V/kN	240	240	100			
	μV/V/N⋅m				9,2	9,2	18,0
Bridge resistance	Ω	700	700	700	350	350	350
Ultimate load, static	%	150	150	150	150	150	150

General Data

Supply voltage ¹⁾	VDC	2,5 15	
Insulation resistance ²⁾	GΩ	>10	
Operating temperature range	°C	-20 80	
Storage temperature range	°C	-30 90	
Amplitude non-linearity (typ.)	%	<1	
Hysteresis (typ.)	%	<1	
Channel cross talk	%	<5	
Bridge zero output (typ. / max.)	mV/V	0,01 / 0,03	
Weight (without cable)	grams	372	
3			

All specifications are typical at 25 $^{\circ}\text{C}$ and rated at 10 V sensor supply voltage, unless otherwise specified.

- 1) With UPS module 9 ... 12 VDC
- ²⁾ All wires to load cell housing, measured with 500 VDC

This information corresponds to the current state of knowledge. Kistler reserves the right to make technical changes. Liability for consequential damage resulting from the use of Kistler products is excluded.

©2013 ... 2016, Kistler Group, Eulachstrasse 22, 8408 Winterthur, Switzerland Tel. +41 52 224 11 11, Fax +41 52 224 14 14, info@kistler.com, www.kistler.com Kistler is a registered trademark of Kistler Holding AG.



measure. analyze. innovate.




Fig. 1: Dummy application, location femur and arm

Cable assembly Fx / Mx Fy / My Fz / Mz red red red purple white yellow yellow yellow purple white black black black purple white blue blue white purple Cable shield

Fig. 2: Cable assembly

Included Accessories

None


Optional Accessories


- Add. label, customized
- UPS module
- Add. shunt

Type No.

M015KABID on request

on request








Fig. 3: Dimensions in mm and direction of action

Page 2/2